FES100A



- Professional equipment
- Powerful and stable motor
- The motor is very quiet
- ULTEM/PEI screw and strainer
- Squeeze jug and collection container in TRITIUM
- Max 30 min use
- The slow juicer also perfectly separates thepulp from the juice, making a beautiful pulp free juice
- Cold pressed, to produce a superior enzyme and nutrient content juice Low
- Auto pulp ejection for continuous automatic juicing
- 2 interchangeable filters optional (coarse screen,fine screen)
- Built in reverse function eliminates clogging for continuous juicing
- Easy clean up
- CE approved

| TECHNICAL SHEET | |
|---------------------------|----------------------|
| Power (Kwatt/Hp) | 0,24 (0,32) |
| Power supply (Volt/Hz) | 230 / 50·60 |
| Utilizzo continuativo | 15 (max 30) |
| Velocità Giri/rpm | 50 |
| Gruppi di macinazione | |
| Net weight (Kg) | 6,5 |
| Gross weight (Kg) | 8,0 |
| Dimensions (mm) | B. 208 D. 448 H. 228 |
| Packaging dimensions (mm) | B. 260 D. 430 H. 400 |